

363P5

# Industrial Plug

## 2CMA166750R1000

Plug, earthing sleeve position 5h, rated current 63A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Black



## GENERAL

|                     |                                   |
|---------------------|-----------------------------------|
| Product Name        | Industrial Plug                   |
| Product ID          | 2CMA166750R1000                   |
| Function            | Plug                              |
| EAN                 | 73926966670                       |
| Catalog Description | Plug, 5h, 63A, IP44, 3P+E         |
| Country of Origin   | Czech Republic (CZ)               |
| E-Number Finland    | 2421625                           |
| E-Number Norway     | 1565179                           |
| E-Number Sweden     | E2416225                          |
| Standards           | IEC 60309-1, -2                   |
| RoHS Status         | Following EU Directive 2011/65/EU |

## TECHNICAL

|                      |                        |
|----------------------|------------------------|
| Product Main Type    | TP                     |
| Color                | Black                  |
| Number of Poles      | 4                      |
| Clock Position       | 5Hour                  |
| Rated Current        | 63 ampere              |
| Rated Voltage        | 600 ... 690 volt       |
| Frequency            | 50 hertz 60 hertz      |
| Degree of Protection | IP44                   |
| Cable Cross-Section  | 4...16 mm <sup>2</sup> |
| Housing Material     | Thermoplastic (PBT)    |
| Plug Angle           | Straight               |
| Product Group        | Tough&Safe             |

## DIMENSIONS

|                    |                |
|--------------------|----------------|
| Product Net Width  | 103 millimetre |
| Product Net Height | 103 millimetre |
| Product Net Length | 215 millimetre |
| Product Net Depth  | 215 millimetre |
| Product Net Weight | 0.64 kilogram  |

## PACKAGING

|                      |                |
|----------------------|----------------|
| Package Width        | 114 millimetre |
| Package Height       | 230 millimetre |
| Package Gross Weight | 0.72 kilogram  |
| Package Length       | 114 millimetre |
| Package Units        | box 1 piece    |