

416C7W

Industrial Connector

2CMA166574R1000

Connector, earthing sleeve position 7h, rated current 16A, IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Black



GENERAL

Product Name	Industrial Connector
Product ID	2CMA166574R1000
Function	Connector
EAN	7392696665742
Catalog Description	Connector, 7h, 16A, IP67, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2416379
E-Number Norway	2416379
E-Number Sweden	E2416379
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TC
Color	Black
Number of Poles	5
Clock Position	7Hour
Rated Current	16 ampere
Rated Voltage	480 ... 500 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	1...2.5 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	86 millimetre
Product Net Height	97 millimetre
Product Net Length	170 millimetre
Product Net Depth	170 millimetre
Product Net Weight	0.32 kilogram

PACKAGING

Package Width	95 millimetre
Package Height	175 millimetre
Package Gross Weight	0.32 kilogram
Package Length	95 millimetre
Package Units	box 1 piece