

232C6W

# Industrial Connector

## 2CMA166584R1000

Connector, earthing sleeve position 6h, rated current 32A, IP67 watertight, 2-poles+earth, frequency 50-60 Hz, color code Blue



## GENERAL

|                     |                                   |
|---------------------|-----------------------------------|
| Product Name        | Industrial Connector              |
| Product ID          | 2CMA166584R1000                   |
| Function            | Connector                         |
| EAN                 | 7392696665841                     |
| Catalog Description | Connector, 6h, 32A, IP67, 2P+E    |
| Country of Origin   | Czech Republic (CZ)               |
| E-Number Finland    | 2421703                           |
| E-Number Norway     | 2416384                           |
| E-Number Sweden     | E2416384                          |
| Standards           | IEC 60309-1, -2                   |
| RoHS Status         | Following EU Directive 2011/65/EU |

## TECHNICAL

|                      |                         |
|----------------------|-------------------------|
| Product Main Type    | TC                      |
| Color                | Blue                    |
| Number of Poles      | 3                       |
| Clock Position       | 6Hour                   |
| Rated Current        | 32 ampere               |
| Rated Voltage        | 200 ... 250 volt        |
| Frequency            | 50 hertz 60 hertz       |
| Degree of Protection | IP67 IP69               |
| Cable Cross-Section  | 2.5...6 mm <sup>2</sup> |
| Housing Material     | Thermoplastic (PBT)     |
| Plug Angle           | Straight                |
| Product Group        | Tough&Safe              |

## DIMENSIONS

|                    |                |
|--------------------|----------------|
| Product Net Width  | 91 millimetre  |
| Product Net Height | 102 millimetre |
| Product Net Length | 184 millimetre |
| Product Net Depth  | 184 millimetre |
| Product Net Weight | 0.392 kilogram |

## PACKAGING

|                      |                |
|----------------------|----------------|
| Package Width        | 135 millimetre |
| Package Height       | 200 millimetre |
| Package Gross Weight | 0.461 kilogram |
| Package Length       | 140 millimetre |
| Package Units        | box 1 piece    |