

332RAU5W

Panel mounted socket

2CMA166962R1000



Socket-outlet, panel mounting, earthing sleeve position 5h, rated current 32A, IP67 watertight, unified flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Black

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA166962R1000
Function	Socket outlet, panel mounting, unified flange, angled
EAN	7392696669627
Catalog Description	Socket-outlet, panel mounting, 5h, 32A, IP67, unified flange, angled, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2409553
E-Number Norway	1561949
E-Number Sweden	2416725
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	95 millimetre
Product Net Height	117 millimetre
Product Net Length	117 millimetre
Product Net Depth	117 millimetre
Product Net Weight	0.21 kilogram

TECHNICAL

Product Main Type	TRAU
Color	Black
Number of Poles	4
Clock Position	5Hour
Rated Current	32 ampere
Rated Voltage	600 ... 690 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	2.5...10 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Angled
Product Group	Tough&Safe

PACKAGING

Package Width	112 millimetre
Package Height	139 millimetre
Package Gross Weight	0.3 kilogram
Package Length	112 millimetre
Package Units	box 1 piece