

316RS6W

# Wall mounted socket

## 2CMA167157R1000



Surface socket-outlet, earthing sleeve position 6h, rated current 16A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Red

## GENERAL

|                     |                                            |
|---------------------|--------------------------------------------|
| Product Name        | Wall mounted socket                        |
| Product ID          | 2CMA167157R1000                            |
| Function            | Surface socket outlet                      |
| EAN                 | 7392696671576                              |
| Catalog Description | Surface socket-outlet, 6h, 16A, IP67, 3P+E |
| Country of Origin   | Czech Republic (CZ)                        |
| E-Number Finland    | 2421208                                    |
| E-Number Norway     | 1543413                                    |
| E-Number Sweden     | E2416532                                   |
| Standards           | IEC 60309-1, -2                            |
| RoHS Status         | Following EU Directive 2011/65/EU          |

## TECHNICAL

|                      |                         |
|----------------------|-------------------------|
| Product Main Type    | TRS                     |
| Color                | Red                     |
| Number of Poles      | 4                       |
| Clock Position       | 6Hour                   |
| Rated Current        | 16 ampere               |
| Rated Voltage        | 380 ... 415 volt        |
| Frequency            | 50 hertz 60 hertz       |
| Degree of Protection | IP67 IP69               |
| Cable Cross-Section  | 1.5...4 mm <sup>2</sup> |
| Housing Material     | Thermoplastic (PBT)     |
| Plug Angle           |                         |
| Product Group        | Tough&Safe              |

## DIMENSIONS

|                    |                |
|--------------------|----------------|
| Product Net Width  | 99 millimetre  |
| Product Net Height | 170 millimetre |
| Product Net Length | 170 millimetre |
| Product Net Depth  | 170 millimetre |
| Product Net Weight | 0.37 kilogram  |

## PACKAGING

|                      |                |
|----------------------|----------------|
| Package Width        | 135 millimetre |
| Package Height       | 200 millimetre |
| Package Gross Weight | 0.37 kilogram  |
| Package Length       | 140 millimetre |
| Package Units        | box 1 piece    |