

363RAU6

Panel mounted socket

2CMA167418R1000



Socket-outlet, panel mounting, earthing sleeve position 6h, rated current 63A, IP44 splashproof, unified flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA167418R1000
Function	Socket outlet, panel mounting, unified flange, angled
EAN	7392696674188
Catalog Description	Socket-outlet, panel mounting, 6h, 63A, IP44, unified flange, angled, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421284
E-Number Norway	1563373
E-Number Sweden	E2416687
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	100 millimetre
Product Net Height	143 millimetre
Product Net Length	143 millimetre
Product Net Depth	143 millimetre
Product Net Weight	0.58 kilogram

TECHNICAL

Product Main Type	TRAU
Color	Red
Number of Poles	4
Clock Position	6Hour
Rated Current	63 ampere
Rated Voltage	380 ... 415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	6...25 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Angled
Product Group	Tough&Safe

PACKAGING

Package Width	112 millimetre
Package Height	139 millimetre
Package Gross Weight	0.62 kilogram
Package Length	112 millimetre
Package Units	box 1 piece