

363BU5

Panel mounted inlet

2CMA167220R1000

Inlet, panel mounting, earthing sleeve position 5h, rated current 63A, IP44 splashproof, unified flange, straight, 3-poles+earth, frequency 50-60 Hz, color code Black



GENERAL

Product Name	Panel mounted inlet
Product ID	2CMA167220R1000
Function	Inlet, panel mounting, unified flange, straight
EAN	73926966727
Catalog Description	Inlet, panel mounting, 5h, 63A, IP44, unified flange, straight, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2417351
E-Number Norway	2417351
E-Number Sweden	E2417351
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	103 millimetre
Product Net Height	103 millimetre
Product Net Length	126 millimetre
Product Net Depth	126 millimetre
Product Net Weight	0.463 kilogram

TECHNICAL

Product Main Type	TBU
Color	Black
Number of Poles	4
Clock Position	5Hour
Rated Current	63 ampere
Rated Voltage	600 ... 690 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	6...25 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Tough&Safe

PACKAGING

Package Width	112 millimetre
Package Height	139 millimetre
Package Gross Weight	0.51 kilogram
Package Length	112 millimetre
Package Units	box 1 piece