

363RAU9

Panel mounted socket

2CMA167422R1000



Socket-outlet, panel mounting, earthing sleeve position 9h, rated current 63A, IP44 splashproof, unified flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA167422R1000
Function	Socket outlet, panel mounting, unified flange, angled
EAN	7392696674225
Catalog Description	Socket-outlet, panel mounting, 9h, 63A, IP44, unified flange, angled, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2416689
E-Number Norway	2416689
E-Number Sweden	2416689
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	100 millimetre
Product Net Height	143 millimetre
Product Net Length	143 millimetre
Product Net Depth	143 millimetre
Product Net Weight	0.58 kilogram

TECHNICAL

Product Main Type	TRAU
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	63 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	6...25 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Angled
Product Group	Tough&Safe

PACKAGING

Package Width	112 millimetre
Package Height	139 millimetre
Package Gross Weight	0.62 kilogram
Package Length	112 millimetre
Package Units	box 1 piece