

316RAM6

Panel mounted socket

2CMA170012R1000



Panel mounted socket, earthing sleeve position 6h, rated current 16A, IP44 splashproof, minimized flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA170012R1000
Function	Panel mounted socket
EAN	73926960122
Catalog Description	Socket-outlet, panel mounting, 6h, 16A, IP44, minimized flange, angled, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421405
E-Number Norway	1564543
E-Number Sweden	E2416468
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	83 millimetre
Product Net Height	89 millimetre
Product Net Length	99 millimetre
Product Net Depth	99 millimetre
Product Net Weight	0.24 kilogram

TECHNICAL

Product Main Type	ERAM
Color	Red
Number of Poles	4
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	380 ... 415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Angled
Product Group	Easy&Safe

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	2.4 kilogram
Package Length	182 millimetre
Package Units	box 10 piece