

316RAU9W

Panel mounted socket

2CMA167016R1000



Socket-outlet, panel mounting, earthing sleeve position 9h, rated current 16A, IP67 watertight, unified flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Panel mounted socket
Product ID	2CMA167016R1000
Function	Socket outlet, panel mounting, unified flange, angled
EAN	73926966166
Catalog Description	Socket-outlet, panel mounting, 9h, 16A, IP67, unified flange, angled, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2416705
E-Number Norway	2416705
E-Number Sweden	E2416705
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	95 millimetre
Product Net Height	102 millimetre
Product Net Length	102 millimetre
Product Net Depth	102 millimetre
Product Net Weight	0.15 kilogram

TECHNICAL

Product Main Type	TRAU
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	16 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	1.5...4 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Angled
Product Group	Tough&Safe

PACKAGING

Package Width	110 millimetre
Package Height	110 millimetre
Package Gross Weight	0.15 kilogram
Package Length	110 millimetre
Package Units	box 1 piece