

4125BS6W

Wall mounted inlet

2CMA167294R1000



Surface Inlet, earthing sleeve position 6h, rated current 125A,
IP67 watertight, 3-poles+neutral+earth, frequency 50-60 Hz,
color code Red

GENERAL

Product Name	Wall mounted inlet
Product ID	2CMA167294R1000
Function	Surface inlet
EAN	7392696672948
Catalog Description	Surface inlet, 6h, 125A, IP67, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421558
E-Number Norway	2417285
E-Number Sweden	E2417285
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TBS
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	125 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	16...70 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Angled
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	145 millimetre
Product Net Height	161 millimetre
Product Net Length	269 millimetre
Product Net Depth	269 millimetre
Product Net Weight	1.59 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	1.73 kilogram
Package Length	182 millimetre
Package Units	box 1 piece