

363BS9W

Wall mounted inlet

2CMA167354R1000



Surface Inlet, earthing sleeve position 9h, rated current 63A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Wall mounted inlet
Product ID	2CMA167354R1000
Function	Surface inlet
EAN	7392696673549
Catalog Description	Surface inlet, 9h, 63A, IP67, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2417266
E-Number Norway	2417266
E-Number Sweden	E2417266
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TBS
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	63 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	6...25 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Angled
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	118 millimetre
Product Net Height	140 millimetre
Product Net Length	251 millimetre
Product Net Depth	251 millimetre
Product Net Weight	1.3 kilogram

PACKAGING

Package Width	152 millimetre
Package Height	265 millimetre
Package Gross Weight	1.3 kilogram
Package Length	120 millimetre
Package Units	box 1 piece