

332RS3W

Wall mounted socket

2CMA167177R1000



Surface socket-outlet, earthing sleeve position 3h, rated current 32A, IP67 watertight, 3-poles+earth, frequency 50-60 Hz, color code red

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA167177R1000
Function	Surface socket outlet
EAN	7392696671774
Catalog Description	Surface socket-outlet, 3h, 32A, IP67, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2406032
E-Number Norway	2416552
E-Number Sweden	E2416552
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	TRS
Color	Red
Number of Poles	4
Clock Position	3Hour
Rated Current	32 ampere
Rated Voltage	380/440 volt
Frequency	50/60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	2.5...10 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	
Product Group	Tough&Safe

DIMENSIONS

Product Net Width	99 millimetre
Product Net Height	178 millimetre
Product Net Length	178 millimetre
Product Net Depth	178 millimetre
Product Net Weight	0.512 kilogram

PACKAGING

Package Width	135 millimetre
Package Height	200 millimetre
Package Gross Weight	0.6 kilogram
Package Length	140 millimetre
Package Units	box 1 piece