

4125BU6W

Panel mounted inlet

2CMA167204R1000



Inlet, panel mounting, earthing sleeve position 6h, rated current 125A, IP67 watertight, unified flange, straight, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Panel mounted inlet
Product ID	2CMA167204R1000
Function	Inlet, panel mounting, unified flange, straight
EAN	73926966747
Catalog Description	Inlet, panel mounting, 6h, 125A, IP67, unified flange, straight, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421557
E-Number Norway	1564896
E-Number Sweden	E2417431
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	127 millimetre
Product Net Height	127 millimetre
Product Net Length	145 millimetre
Product Net Depth	145 millimetre
Product Net Weight	1 kilogram

TECHNICAL

Product Main Type	TBU
Color	Red
Number of Poles	5
Clock Position	6Hour
Rated Current	125 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP67 IP69
Cable Cross-Section	16...70 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	Straight
Product Group	Tough&Safe

PACKAGING

Package Width	135 millimetre
Package Height	200 millimetre
Package Gross Weight	1.1 kilogram
Package Length	140 millimetre
Package Units	box 1 piece