

332RS11

Wall mounted socket

2CMA193134R1000



Wall mounted socket, earthing sleeve position 11h, rated current 32A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Red

GENERAL

Product Name	Wall mounted socket
Product ID	2CMA193134R1000
Function	Wall mounted socket
EAN	7392696931342
Catalog Description	Industrial Socket Outlets for Surface Mounting, 3P+E, 32 A, 440 ... 460 V
Country of Origin	Czech Republic (CZ)
E-Number Finland	2416501
E-Number Norway	2416501
E-Number Sweden	2416501
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	85 millimetre
Product Net Height	118 millimetre
Product Net Length	163 millimetre
Product Net Depth	163 millimetre
Product Net Weight	0.28 kilogram

TECHNICAL

Product Main Type	ERS
Color	Red
Number of Poles	4
Clock Position	11Hour
Rated Current	32 ampere
Rated Voltage	440 ... 460 volt
Frequency	60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...10 mm ²
Housing Material	Plastic (PA)
Plug Angle	
Product Group	Easy&Safe

PACKAGING

Package Width	188 millimetre
Package Height	428 millimetre
Package Gross Weight	2.8 kilogram
Package Length	175 millimetre
Package Units	box 10 piece