

316R6

Panel mounted socket

2CMA193154R1000

Panel mounted socket, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red



GENERAL

Product Name	Panel mounted socket
Product ID	2CMA193154R1000
Function	Panel mounted socket
EAN	73926969315
Catalog Description	Socket-outlet, panel mounting, 6h, 16A, IP44, minimized flange, straight, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421234
E-Number Norway	1547313
E-Number Sweden	E2416609
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	66 millimetre
Product Net Height	87 millimetre
Product Net Length	88 millimetre
Product Net Depth	88 millimetre
Product Net Weight	0.25 kilogram

TECHNICAL

Product Main Type	ER
Color	Red
Number of Poles	4
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	380 ... 415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	2.5 kilogram
Package Length	158 millimetre
Package Units	box 10 piece