

CUED 416-6+RD

Panel mounted socket

2CMA178696R1000

Surface socket-outlet, for surface mounting, earthing sleeve position 6h, rated current 16A, IP44 splashproof, 3-poles+neutral+earth, frequency 50-60 Hz, color code Red



GENERAL

Product Name	Panel mounted socket
Product ID	2CMA178696R1000
Function	Socket outlet for surface mounting
EAN	7392696786966
Catalog Description	Surface socket-outlet, for surface mounting, 6h, 16A, IP44, 3P+N+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2416011
E-Number Norway	2416011
E-Number Sweden	E2416011
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	95 millimetre
Product Net Height	95 millimetre
Product Net Length	62 millimetre
Product Net Depth	62 millimetre
Product Net Weight	0.31 kilogram

TECHNICAL

Product Main Type	CUED
Color	Colour: Grey Identification colour: Red
Number of Poles	5
Clock Position	6Hour
Rated Current	16 ampere
Rated Voltage	200/346 ... 240/415 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Thermoplastic (PBT)
Plug Angle	
Product Group	Special Plugs & Sockets

PACKAGING

Package Width	188 millimetre
Package Height	428 millimetre
Package Gross Weight	3.1 kilogram
Package Length	175 millimetre
Package Units	box 10 piece