

316BS7

Wall mounted inlet

2CMA193299R1000



Wall mounted inlet, earthing sleeve position 7h, rated current 16A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Black

GENERAL

Product Name	Wall mounted inlet
Product ID	2CMA193299R1000
Function	Wall mounted inlet
EAN	7392696932998
Catalog Description	Surface inlet, 7h, 16A, IP44, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2417169
E-Number Norway	2417169
E-Number Sweden	E2417169
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EBS
Color	Black
Number of Poles	4
Clock Position	7Hour
Rated Current	16 ampere
Rated Voltage	480 ... 500 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Angled
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	78 millimetre
Product Net Height	68 millimetre
Product Net Length	118 millimetre
Product Net Depth	118 millimetre
Product Net Weight	0.19 kilogram

PACKAGING

Package Width	154 millimetre
Package Height	378 millimetre
Package Gross Weight	1.9 kilogram
Package Length	182 millimetre
Package Units	box 10 piece