

332RAU9

# Panel mounted socket

## 2CMA193276R1000

Panel mounted socket, earthing sleeve position 9h, rated current 32A, IP44 splashproof, unified flange, angled, 3-poles+earth, frequency 50-60 Hz, color code Blue



## GENERAL

|                     |                                                                            |
|---------------------|----------------------------------------------------------------------------|
| Product Name        | Panel mounted socket                                                       |
| Product ID          | 2CMA193276R1000                                                            |
| Function            | Panel mounted socket                                                       |
| EAN                 | 7392696932769                                                              |
| Catalog Description | Socket-outlet, panel mounting, 9h, 32A, IP44, unified flange, angled, 3P+E |
| Country of Origin   | Czech Republic (CZ)                                                        |
| E-Number Finland    | 2416668                                                                    |
| E-Number Norway     | 2416668                                                                    |
| E-Number Sweden     | 2416668                                                                    |
| Standards           | IEC 60309-1, -2                                                            |
| RoHS Status         | Following EU Directive 2011/65/EU                                          |

## DIMENSIONS

|                    |                |
|--------------------|----------------|
| Product Net Width  | 110 millimetre |
| Product Net Height | 110 millimetre |
| Product Net Length | 116 millimetre |
| Product Net Depth  | 116 millimetre |
| Product Net Weight | 0.26 kilogram  |

## TECHNICAL

|                      |                          |
|----------------------|--------------------------|
| Product Main Type    | ERAU                     |
| Color                | Blue                     |
| Number of Poles      | 4                        |
| Clock Position       | 9Hour                    |
| Rated Current        | 32 ampere                |
| Rated Voltage        | 200 ... 250 volt         |
| Frequency            | 50 hertz 60 hertz        |
| Degree of Protection | IP44                     |
| Cable Cross-Section  | 2.5...10 mm <sup>2</sup> |
| Housing Material     | Plastic (PA)             |
| Plug Angle           | Angled                   |
| Product Group        | Easy&Safe                |

## PACKAGING

|                      |                |
|----------------------|----------------|
| Package Width        | 188 millimetre |
| Package Height       | 428 millimetre |
| Package Gross Weight | 2.6 kilogram   |
| Package Length       | 175 millimetre |
| Package Units        | box 10 piece   |