

216BS4

Wall mounted inlet

2CMA193289R1000



Wall mounted inlet, earthing sleeve position 4h, rated current 16A, IP44 splashproof, 2-poles+earth, frequency 50-60 Hz, color code Yellow

GENERAL

Product Name	Wall mounted inlet
Product ID	2CMA193289R1000
Function	Wall mounted inlet
EAN	7392696932899
Catalog Description	Surface inlet, 4h, 16A, IP44, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2420041
E-Number Norway	1542361
E-Number Sweden	E2417161
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EBS
Color	Yellow
Number of Poles	3
Clock Position	4Hour
Rated Current	16 ampere
Rated Voltage	100 ... 130 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Angled
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	65 millimetre
Product Net Height	66 millimetre
Product Net Length	115 millimetre
Product Net Depth	115 millimetre
Product Net Weight	0.15 kilogram

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	1.5 kilogram
Package Length	158 millimetre
Package Units	box 10 piece