

316B9

Panel mounted inlet

2CMA193348R1000

Panel mounted inlet, minimized flange, straight, earthing sleeve position 9h, rated current 16A, IP44 splashproof, 3-poles+earth, frequency 50-60 Hz, color code Blue



GENERAL

Product Name	Panel mounted inlet
Product ID	2CMA193348R1000
Function	Panel mounted inlet
EAN	7392696933483
Catalog Description	Inlet, panel mounting, 9h, 16A, IP44, minimized flange, straight, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2417335
E-Number Norway	2417335
E-Number Sweden	E2417335
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	66 millimetre
Product Net Height	66 millimetre
Product Net Length	68 millimetre
Product Net Depth	68 millimetre
Product Net Weight	0.13 kilogram

TECHNICAL

Product Main Type	EB
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	16 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	1.5...4 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	1.3 kilogram
Package Length	158 millimetre
Package Units	box 10 piece