

232BU6

Panel mounted inlet

2CMA193434R1000



Panel mounted inlet, earthing sleeve position 6h, rated current 32A, IP44 splashproof, unified flange, straight, 2-poles+earth, frequency 50-60 Hz, color code Blue

GENERAL

Product Name	Panel mounted inlet
Product ID	2CMA193434R1000
Function	Panel mounted inlet
EAN	7392696934343
Catalog Description	Inlet, panel mounting, 6h, 32A, IP44, unified flange, straight, 2P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2421542
E-Number Norway	1544032
E-Number Sweden	E2417341
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

TECHNICAL

Product Main Type	EBU
Color	Blue
Number of Poles	3
Clock Position	6Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...10 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

DIMENSIONS

Product Net Width	75 millimetre
Product Net Height	75 millimetre
Product Net Length	80 millimetre
Product Net Depth	80 millimetre
Product Net Weight	0.150 kilogram

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	1.5 kilogram
Package Length	158 millimetre
Package Units	box 10 piece