

332BU9

Panel mounted inlet

2CMA193444R1000

Panel mounted inlet, earthing sleeve position 9h, rated current 32A, IP44 splashproof, unified flange, straight, 3-poles+earth, frequency 50-60 Hz, color code Blue



GENERAL

Product Name	Panel mounted inlet
Product ID	2CMA193444R1000
Function	Panel mounted inlet
EAN	7392696934442
Catalog Description	Inlet, panel mounting, 9h, 32A, IP44, unified flange, straight, 3P+E
Country of Origin	Czech Republic (CZ)
E-Number Finland	2417345
E-Number Norway	2417345
E-Number Sweden	E2417345
Standards	IEC 60309-1, -2
RoHS Status	Following EU Directive 2011/65/EU

DIMENSIONS

Product Net Width	75 millimetre
Product Net Height	75 millimetre
Product Net Length	80 millimetre
Product Net Depth	80 millimetre
Product Net Weight	0.17 kilogram

TECHNICAL

Product Main Type	EBU
Color	Blue
Number of Poles	4
Clock Position	9Hour
Rated Current	32 ampere
Rated Voltage	200 ... 250 volt
Frequency	50 hertz 60 hertz
Degree of Protection	IP44
Cable Cross-Section	2.5...10 mm ²
Housing Material	Plastic (PA)
Plug Angle	Straight
Product Group	Easy&Safe

PACKAGING

Package Width	138 millimetre
Package Height	345 millimetre
Package Gross Weight	1.7 kilogram
Package Length	158 millimetre
Package Units	box 10 piece