





R: for round cable

MATERIAL & FINISH

Body: PC. UL94V-2, clean

Contact: copper alloy, underplated 100uin Nickel,
and hard gold plated on contact region,
gold flash plated on remainder of terminal.

SPECIFICATION

Voltage Rating: 125 volts AC, at 1.5 amps.
Dielectric Withstanding Voltage: 1000 volts AC.
Insulation Resistance: 500 megaohms min.
Contact Resistance: 30 milliohms max.
Durability: 750 cycles.
Temp. Rating: -40°C to +85°C

	A
6P2C	5.20
6P4C	5.20
6P6C	7.15

UNIT: m / m
TOL.: +/- 0.10

RoHS
Compliant

APPD.
核准

DWG.
製圖

DATE 制表日

Helen

2024/5/8



SCALE
比例

UNIT
單位

PAGE
張數

TOLERANCE
容許公差

SIZE.
紙張尺寸

REV.
版次

1 OF 1

Ninigi

PART NAME 品名

MODULAR PLUG 6PXC ROHS

PART NO.

料號

RJ11