

Red's Music Audio Cable - Stereo Jack 6.3mm / Stereo Jack 6.3mm socket

Description:

The Red's Music cable is a high-quality cable, ideal for demanding users who value excellent sound quality and reliability. Made from the finest materials, it provides excellent signal conductivity without unwanted interference or noise. Professional cable with two symmetrically twisted cores shielded with mesh braid. Cable with stabilizing cotton filling in a flexible, matte PVC sheath that eliminates the effects of light reflections. Dedicated to fixed and mobile applications in stage and studio audio installations and sound systems. The wires are handmade in Poland, and each cable is tested, which ensures 100% efficiency in connection. Each cable has a protection to protect it from pulling out.

Specification:

Product type: Audio cable

Version: Standard

Symbol: AU24...BX

Colour: Black

Length: from 0.3m to 20m

Connector 1: Stereo Jack 6.3mm

Connector 2: Stereo Jack 6.3mm socket

Connector model: J55, JG09

Inner cable: 2 x 0.23mm²

Shielding: stranded copper (mesh braid - ≥90% coverage)

Core insulation: PE - transparent, red

Filling: cotton

Sheath insulation: PVC

Cable outer diameter: 6 mm

Special features: Plugs soldered with lead-free tin with the addition of silver. The connectors have a cable pull-out protection. For cables over 3m additionally Velcro for fastening

Technical data of the cable used:



Cable model: MIC-100 - (2x0.23mm²)

Operating temperature: -25°C to 65°C (fixed installations) / -5°C to 65°C (moving installations)

Minimum laying temperature: -5°C

Capacitance (1kHz): core-shield: ≤130nF/km / wire-core: ≤65nF/km

Impedance: 85Ω ±5Ω

Core resistance: 71.5Ω/km DC

Screen resistance: 18.0Ω/km DC


Insulation resistance: >1.0GΩ/km

Minimum bend radius: 30mm - 5x∅ (∅ - outer diameter)

Cable outer diameter: 6.0mm

Weight: About 51kg/km

Wiring:



AU24...BX



Type of plugs used:

	
J55 - Stereo Jack 6.3	JG09 - stereo jack 6.3 socket

Available models:

Product Code	Length	Scales*	GTIN-13
AU2403BX	0.3 m	77g	5903867410164
AU2405BX	0.5 m	86g	5903867410171
AU2410BX	1.0 m	108g	5903867410188
AU2415BX	1.5 m	131g	5903867410195
AU2420BX	2.0 m	153g	5903867410201
AU2430BX	3.0 m	198g	5903867410218
AU2440BX	4.0 m	250g	5903867410225
AU2450BX	5.0 m	295g	5903867410232
AU2460BX	6.0 m	340g	5903867410249
AU2470BX	7.0 m	385g	5903867410256
AU2480BX	8.0 m	430g	5903867410263
AU2490BX	9.0 m	475g	5903867410270
AU24100BX	10.0 m	520g	5903867410287
AU24150BX	15.0 m	760g	5903867410294
AU24200BX	20.0 m	985g	5903867410300

* Zawiera wagę przewodu i opakowania.

Wagi są wartościami teoretycznymi i mogą różnić się dla poszczególnych produktów