

FSC-215 HI-FI

Speaker cable 2x1,5mm² OFC Flat PVC



Professional, flat speaker cable with two parallel conductors. Cable in a flexible PVC jacket that reduces light reflection effects. Dedicated to fixed and mobile applications in home and studio hi-fi audio installations.

Cable construction:

- **Cores:** copper stranded 2x1,5mm²
- **Shield:** -
- **Filling:** -
- **Core insulation:** PE - black, red
- **Jacket insulation:** PVC - black with red stripe

Technical data:

- **Working temperature:** -30°C to 75°C (fixed installations) / -20°C to 75°C (mobile installations)
- **Minimum laying temperature:** -5°C
- **Conductor resistance:** 12,8Ω/km DC
- **Insulation resistance:** >20,0MΩ/km
- **High voltage test:** 2,0kV/50Hz
- **Minimum bending radius:** 25mm - 5x∅ (∅ - outside diameter)
- **External dimensions:** approximately 8,9mm x 4,8mm
- **Weight:** approximately 73kg/km