

Model Number: 4G-PNL02

PRODUCT SPECIFICATION

I. Main features

***Electrical**

No.	Item	Specifications
1	Frequency (MHz)	680-960/1710-2700
2	Gain (Zenith)	8dBi
3	V.S.W.R	<2
4	Impedance	50Ω
5	Beamwidth (°)	H: 70/60, V: 55/45
6	Max Input Power	50W
7	Radiation	Omni-directional
8	Polarization	Linear

***Mechanical**

No.	Item	Specifications
1	Cable	RG 58, 3m or others
2	Connector	SMA-J, N-female, or others
3	Dimensions (cm)	21x18x4,3
4	Weight (kg)	0,6
5	Mounting method	Pole/ Wall mount
6	Wind Velocity (m/s)	60
7	Working Temperature	-40°C~+85°C
8	Working Humidity	5~95%

II. Appearance

