




UQS-COB-5W-NW-24V-50m

Professional Led Strip, 5W/m




■ Features:

- Uniform lighting
- Uniform light line and high luminous intensity
- 3 years warranty



TECHNICAL DETAILS

MODEL	UQS-COB-5W-NW-24V-50m	EPREL
Supply voltage	24V $\pm$ 0.5Vdc	
Power	5W/m	
Current	0,21 A/m	
Power per reel	25W	
Color temperature	4000K	
Beam angle	180°	
Luminous flux	600 lm/m	
CRI	>90	
Maximum length for one sided supply	5m	
IP protection degree	IP20	
Working temperature	-20°C ÷ 50°C	
Storage temperature	-30°C ÷ 80°C	
LED QTY	320 LEDs/m	
Width PCB	8mm	
Cut section	50mm	
Connection wire	2 x AWG20 (0.52 mm ²) stranded wire, length = 360 mm: V+: red: V-: black.	
Dimensions (L x W x H)	50000 x 8 x 2.2 mm	
Packing	50m / reel (bag)	



MECHANICAL SPECIFICATION:

