




Mark:

Item 1: Heat shrinkable sleeve, transparent, radiation cross-linked modified polyolefin.

Item 2: Solder rings with flux.

Item 3: Meltable rings.

ITEM	TOLERANCE	$L \pm 2.0$	D_{Min}	Qty Item 2	Color Item 3	Wire Dimensions						
						ϕB_{Min}	ϕB_{Min} ϕC_{Max}	ϕC_{Min}				
尺寸 SIZE		40.0	2.7	1	Red	1.4	2.7	1.4				

TERMINAL MATERIALS			UNIT: mm
Metal THICKNESS		WIRE RANGE	22-16 AWG 0.5-1.5mm ²
INSULATION MATERIALS	Polyolefin	OPERATING TEMPERATURE AND VOLTAGE	-55~125℃ 600 VOLTS MAX.
		MAXIMUM ELECTRICAL RATING	19A