



	1	2	3	4	5	6	7	8			
A	Raw Material		PA66 SILICONE COPPER ALLOY	3 PIN 							
	Flame-resistant rating		UL94 V-2								
	Level of protection		IP68								
B	Voltage rating/Current rating		450 V / 24 A								
	Withstanding voltage		2500 V								
	Cable gague		0.5~2.5mm ²								
C	Operating temperature		-40~105 °C								
D	Type	Rubbers Diameter(d)	Outer Cable Diameter								
	A	φ 14.5 mm	φ 10~14 mm								
	B	φ 12 mm	φ 9~12 mm								
	C	φ 8.5 mm	φ 5~9 mm								
E	Rubbers Diameter										
F											
G											
H											
	1	2	3	4	5	6	7	8			

RoHS Compliant		HSM 玄茂科技股份有限公司 HSUAN MAO TECHNOLOGY CO., LTD.	
APPD. 核准		TOLERANCE 容許公差	PART NAME 品名
DWG. 製圖 Helen	SCALE 比例 參考	.0 ± 0.35 .00 ± 0.25 ANG. ± 5°	M25 TYPE WATERPROOF CONNECTOR 3PIN WATERPROOF GRADE:IP68 24A 450V T/L:108MM(REF.) BODY MATERIAL:PA66 UL94V-2 BLACK COLOR ROHS
DATE 制表日 2025/01/06	UNIT 單位 MM	SIZE 紙張尺寸 A 4	PART NO.
	PAGE 張數 1 OF 1	REV. 版本 A	料號 C9455-03AB(A,B,C)000R