



HQS-9.6W-120LED-NW-24V-50m

Professional Led Strip, 9.6 W/m



4000K
NEUTRAL WHITE

■ Features:

- Double copper layer
- Can be cut every segment 5 cm
- 3 years warranty




TECHNICAL DETAILS

MODEL	HQS-9.6W-120LED-NW-24V-50m
Supply voltage	24V $\pm$ 0.5Vdc
Power	9.6W/m
Current	0.4 A/m
Power per reel	48W
Color temperature	4000K
Beam angle	120°
Luminous flux	1000 lm/m
CRI	>80
Maximum length for one sided supply	5m
IP protection degree	IP33
Working temperature	-25°C $\div$ 50°C
Storage temperature	-30°C $\div$ 60°C
LED QTY	120 LEDs/m
Width PCB	8mm
Cut section	50mm
Connection wire	2 x AWG20 (0.52 mm ²) stranded wire, length = 140 mm: V+: red: V-:black.
Dimensions (L x W x H)	50000 x 8 x 1.2 mm
Packing	50m / reel (bag)



MW LIGHTING

HQS-9.6W-120LED-NW-24V



5
kWh/1000h



2019/2015

MECHANICAL SPECIFICATION:

