



HQS-12W-60LED-WW-12V

Professional Led Strip, 12 W/m



■ Features:

- Double copper layer
- Can be cut every segment 5 cm
- 3 years warranty



3000K
WARM WHITE

IP33

CRI>80

120°
lens

UK
CA

CE

3
year warranty

TECHNICAL DETAILS

MODEL	HQS-12W-60LED-WW-12V	EPREL
Supply voltage	12V $\pm$ 0.5Vdc	ENERGY MW LIGHTING HQS-12W-60LED-WW-12V A B C D E F G 6 kWh/1000h 2019/2015
Power	12W/m (30W/reel)	
Current	1 A/m (5A/roll)	
Power per reel	60W	
Color temperature	3000K	
Beam angle	120°	
Luminous flux	1220 lm/m (5900lm/roll)	
CRI	>80	
Maximum length for one sided supply	5m	
IP protection degree	IP33	
Working temperature	-25°C ÷ 50°C	
Storage temperature	-25°C ÷ 60°C	
LED QTY	60 LEDs/m (300 LEDs/reel)	
Width PCB	10mm	
Cut section	50mm	
Connection wire	2 x AWG20 (0.52 mm ²) stranded wire, length = 140 mm: V+: red: V-:black.	
Dimensions (L x W x H)	5000 x 10 x 1.2 mm	
Packing	5m / reel (bag)	

MECHANICAL SPECIFICATION:

