



UQS-COB-12W-NW-24V

Professional Led Strip, 12W/m



■ Features:

- Uniform lighting
- Uniform light line and high luminous intensity
- 3 years warranty

4000K
NEUTRAL WHITE



TECHNICAL DETAILS

MODEL	UQS-COB-12W-NW-24V	EPREL
Supply voltage	24V $\pm$ 0.5Vdc	
Power	12W/m (60W/reel)	
Current	0.5 A/m (2.5A/roll)	
Power per reel	60W	
Color temperature	4000K	
Beam angle	180°	
Luminous flux	1180 lm/m (5900lm/roll)	
CRI	>90	
Maximum length for one sided supply	5m	
IP protection degree	IP20	
Working temperature	-20°C ÷ 50°C	
Storage temperature	-30°C ÷ 80°C	
LED QTY	480 LEDs/m (4805 LEDs/reel)	
Width PCB	10mm	
Cut section	50mm	
Connection wire	2 x AWG20 (0.52 mm ²) stranded wire, length = 360 mm: V+: red: V-: black.	
Dimensions (L x W x H)	5004 x 10 x 2.2 mm	
Packing	5m / reel (bag)	



MW LIGHTING

UQS-COB-12W-NW-24V



6
kWh/1000h



2019/2015

MECHANICAL SPECIFICATION:

