



UQS-COB-12W-NW-12V-5m

Professional Led Strip, 12W/m



■ Features:


- Uniform lighting
- Uniform light line and high luminous intensity
- 3 years warranty

4000K
NEUTRAL WHITE



TECHNICAL DETAILS

MODEL	UQS-COB-12W-NW-12V-5m	EPREL
Supply voltage	12V $\pm$ 0.5Vdc	
Power	12W/m	
Current	1 A/m	
Power per reel	60W	
Color temperature	4000K	
Beam angle	180°	
Luminous flux	1240 lm/m	
CRI	>90	
Maximum length for one sided supply	5m	
IP protection degree	IP20	
Working temperature	-20°C ÷ 50°C	
Storage temperature	-30°C ÷ 80°C	
LED QTY	480 LEDs/m	
Width PCB	10mm	
Cut section	25mm	
Connection wire	2 x AWG20 (0.52 mm ²) stranded wire, length = 360 mm: V+: red: V-:black.	
Dimensions (L x W x H)	5000 x 10 x 2.2 mm	
Packing	5m / reel (bag)	



MECHANICAL SPECIFICATION:

