

圖號 DRAWING No. :				校訂版次 REVISIONS			
品名 NAME: Ring		ITEM No. :		版次	記述 DESCRIPTION	DATE	核可

MAXIMUM ELECTRIC CURRENT

A. W. G	22	20	18	16
MAX AMP	9	12	17	18

NOTE:


1. MAXIMUM ELECTRICAL RATING: 105°C 600 VOLTS


2. WIRE RANGE: 22-16 AWG / 0.5-1.5 mm²
INSULATED COLOR: RED

3. MATERIAL THICKNESS: t
TOLERANCE: ±0.05



WIRE RANGE AWG/mm ²	產品編號 ITEM NO.	d2 ±0.20	B ±0.20	F ±0.30	L ±1.00	E ±0.60	D ±0.30	d1 ±0.20	t
22-16 AWG 0.5-1.5 mm ²	ST-082/R	2.2	6.6	6.3	19.6	10.0	4.1	1.7	0.75
		3.2	5.5	4.0	16.7				
		3.7	5.5	4.0	16.7				
		3.7	6.6	6.3	19.6				
		3.7	8.0	7.0	21.0				
		4.3	6.6	6.3	19.6				
		4.3	8.0	7.0	21.0				
		5.3	8.0	7.0	21.0				
		6.5	11.6	11.1	26.8				
		8.4	11.6	11.1	26.8				
		10.5	13.6	13.9	30.7				
		13.0	19.2	16.0	35.6				



認可 APPROVALS		第三視角 THIRD VIEW	MATERIAL	單位 UNIT	日期 DATE: 2015. 01. 05
製圖 DRAFT:	TINA		INSULATION: VINYL	m/m	
設計 DESIGN:	KEN		MATERIAL: COPPER	比例 SCALE	
核可 CHECKED:	ANDY		TIN PLATING		