

Material:

- Item ④ Clamp: Brass, Ni plated
- Item ⑤ Terminal screw: Steel Zinc plating “-” slot type.
- Item ⑥ Wire guard solder pin: Brass, Tin plated
- Item ⑦ Terminal housing: Thermoplastic (UL 94V-0)

- Voltage rating: 300V
- Current rating: 10A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque: 3.5 Lb-In
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6 KV
- Operating temperature: -40°C to +115°C
- Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: us
- Critical dimension: 

04	4 POLES	0 Black (RAL9005)	000	"@" Logo
05	5 POLES	2 Red (RAL3001/D)	00A	"ANYTEK" Mark
	:	3 Orange (RAL2011/P)		
24	24 POLES	4 Yellow (RAL1018/A)		Any special item by
		5 Green (RAL6018/T)		customer request.
		6 Blue (RAL5015/A)		please contact sales
		8 Grey (RAL7035/D)		department.
		9 White (RAL1102)		
		C Grey (RAL6018/U)		

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

5	6	7
---	---	---

N=Number of poles

