







Poles	2x2	2x3	2x4	2x5	2x6	2x7	2x8	2x9	2x10	2x11	2x12	2x13
Dim L	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96	66.04
Dim B	5.08	10.16	15.24	20.32	25.40	30.48	35.56	40.64	45.72	50.80	55.88	60.96
TOL	±0.20					±0.30					±0.35	
Poles	2x14	2x15	2x16	2x17	2x18	2x19	2x20	2x21	2x22	2x23	2x24	
Dim L	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	121.92	
Dim B	66.04	71.12	76.20	81.28	86.36	91.44	96.52	101.60	106.68	111.76	116.84	
TOL	±0.35					±0.40						
Poles	2x25	2x26	2x27	2x28	2x29	2x30	2x31	2x32				
Dim L	127.0	132.08	137.16	142.24	147.32	152.4	157.48	162.56				
Dim B	121.92	127.0	132.08	137.16	142.24	147.32	152.4	157.48				
TOL	±0.50					±0.60						

SIGN	DATE	DESCRIPTION	APPROVER
△	01/18/07	Soldering temperature changed from 245° to 250°	Tason
△	01/18/07	Part No is Changed	Tason
△	03/25/09	Add the tolerance table	Jacke
△	10/28/13	Update the drawing	Guoxue
THIS IS CAD DRAWING, DO NOT REVISE MANUALLY!!!			

Material

- Item① Terminal housing :Thermoplastic (UL 94V-0)
- Item② Clamp : Brass ,Ni plated
- Item③ Wire guard solder pin :Brass ,Tin plated
- Item④ Terminal screw: Steel Zinc plating"-slot type

Electrical

- Voltage rating: 300VAC
- Current rating: 20A
- Wire range:
- Solid wire(AWG): 12-22
- Stranded wire(AWG): 12-22
- Torque(Lb-In): 3.5
- Screw: M2.5
- Wire strip length: 6-7mm
- Withstanding Voltage: 1.6KV
- Operating temperature: -40°C to +115°C
- △△ Soldering temperature: 260°C±5°C/5 Sec
- Safety Approval: 

- Critical dimension: 

△△ YL xx 6 1 x 0 xxxx G

04 2x2 POLES
06 2x3 POLES
...
64 2x32 POLES

COLOR

0 Black (RAL9005)
2 Red (RAL3001/D)
3 Orange(RAL2011/P)
4 Yellow(RAL1018/A)
5 Green(RAL6018/T)
6 Blue (RAL5015/A)
8 Grey(RAL7035/D)
9 White(RAL1102)
C Green(RAL6018/U)

G RoHS compliant
(lead<4%)
In copper Alloy

0000 @ logo
000A ANYTEK logo
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

ANYTEK

CUSTOMER COPY

ALL RIGHTS RESERVED. REPRODUCTION OR ISSUE TO THIRD PARTIES IN ANY FORM WHATEVER IS NOT PERMITTED WITHOUT WRITTEN AUTHORITY FROM THE PROPRIETOR. PROPERTY OF ANYTEK TECHNOLOGY CO., LTD

TITLE	YL-5.08mm Series "- Right						
PART NO.	YLxx61x0xxxxG			DWG NO.	8YL0102		
APPROVED	CHECKED	DESIGNED	DRAWN	CUST NO.			
		Evan 2014.10.23	Evan 2014.10.23		UNIT: mm	Tolerance	
					SCALE: NONE	X.X ±0.50	
						X.XX ±0.30	
						X° ±1°	
				SHEET: 01/01	REV.: F		