

HX

XX

Number of contacts

X

Pitch

X

Insulator

X

Color

X

Body type

X

X

X

X

X

End Stackable
01 1 contacts
02 2 contacts
03 3 contacts
.. ...
24 24 contacts

0 5.0/.197"

2 3.5/.138"

0 Vertical(90D wire inlet)
1 Horizontal(180D wire inlet)

0 Vertical(90D wire inlet)
-Interlace(A type)(only pitch 3.5mm)
1 Vertical(Single contact)
(90D wire inlet)(B type)(only pitch 3.5mm)
2 Horizontal(180D wire inlet)
-Interlace(A type)(only pitch 3.5mm)
3 Horizontal(180D wire inlet)
(B type)(Double contact)(only pitch 3.5mm)
4 Horizontal(90D wire inlet)
(B type)(Double contact)(only pitch 3.5mm)

0 Black
2 Red
(RAL 3001/D)
5 Green
(RAL 6018/T)
8 Grey
(RAL 7004/P)
9 White
(RAL 1002)
C Multiple colors

0 Bevel angle
(only pitch 5.0)
1 Right angle

0000 Standard

Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy