

HA

XX
Number of contacts

X
Pitch

X
Insulator

X
Color

0

X

X

X

X

X

End Stackable
01 1 contacts
02 2 contacts
03 3 contacts
.. ..
24 24 contacts
(pitch 2.54&3.81&5.0&5.08)
16 16 contacts
(pitch 7.5&7.62)
12 12 contacts
(pitch 10.0&10.16)

0 5.08/.20"
2 7.62/.30"
3 5.0/.197"
4 10.0/.394"
5 2.54/.10"
6 7.5/.295"
7 3.81/.15"

0 Vertical
(90D wire inlet)
1 Horizontal
(180D wire inlet)

0 Black
2 Red
5 Green
(RAL 6018/T)
8 Grey
(RAL 7004/P)
C Multiple colors

0000 Standard

Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy