

KI

XX

Number of contacts

X

Pitch

0

X

Color

X

Body type

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
... ...
24 24 contacts

3 3.81/.15"
5 5.08/.20"

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0 W/O flange
1 W/O flange
(with high profile)
2 With flange
3 With flange
(with high profile)

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy
H ROHS compliant
(lead<1000ppm)
In copper alloy