

EJ

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Pin type

X

X

X

X

X

End Stackable
01 1 contacts
02 2 contacts
03 3 contacts
.. ...
06 06 contacts

D 19.0/.748"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "- " Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

1 Middle contact(double)+
side contact(double) W/O flange

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy
H ROHS compliant
(lead<1000ppm)
In copper alloy