

ET

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Body type

X **X** **X** **X** **X**

Solid Block
02 2 contacts
03 3 contacts
.. ..
16 16 contacts
(pitch 7.62)
08 8 contacts
(pitch 15.24)

0 7.62/.30"
1 15.24/.60"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp
2 "*" Posidriv screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

Used for VC series(300V 32A)
0 Without flange
2 With flange(W/O handle)
3 W/flange & W/handle
(only 3p & 4p)

Used for KT series(600V 41A)
A Without flange
C With flange(W/O handle)
D W/flange & W/handle
(only 3p & 4p)

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

Used for VC series(300V 41A)
E Without flange
G With flange(W/O handle)

G ROHS compliant
(lead<4%)
In copper alloy
H ROHS compliant
(lead<1000ppm)
In copper alloy