

KE

XX

Number of contacts

X

Pitch

X

Body type

X

Color

X

PCB mounting

X

X

X

X

X

Solid Block
04 2*2 contacts
06 2*3 contacts
.. ...
48 2*24 contacts

1 3.5/.138"
3 3.81/.15"

THR type
A Close
B With flange
C With latch holder

DIP type
1 Close
2 With flange
3 With latch holder

THR type
0 Black

DIP type
0 Black 6 Blue
2 Red 8 Grey
3 Orange 9 White
4 Yellow C Green
5 Green (RAL 6018/U)
(RAL 6018/T)

0 Vertical
1 Right angle

0000 THR type
A000 DIP type

Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy