

KZ

XX Number of contacts					X Pitch	X Screw&Terminal	X Color	X Cage type	X	X	X	X	X
1 3.5/.138" 2 7.0/.276" 7 5.0/.197" 8 10.0/.394"					0 "+/-" Combination type W/Brass Machined Clamp 1 "- " Slotted screw W/Brass Machined Clamp	0 Black 5 Green (RAL 6018/T) 6 Blue 8 Grey (RAL 7035/D) C Green (RAL 6018/U)	0 Square hole 1 Round hole	0000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.	G ROHS compliant (lead<4%) In copper alloy				