

NQ

XX
Number of contacts

X
Pitch

X
Body type

X
Color

0

X

X

X

X

X

End Stackable
01 1 contacts
02 2 contacts
03 3 contacts
.. ..
10 10 contacts

0 2.5/0.10"
1 5.0/0.20"
2 4.0/0.16"
3 8.0/0.31"

0 With flange
(Only 2.5&5.0)
1 Without flange

0 Black
1 Natural color
8 Grey

0000 Standard

**Any special item by
customer request,
please contact sales
department.**

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy