

OP

XX

Number of contacts

X

Pitch

X

Pin length

X

Pin plating

X

Material of body

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
...
24 24 contacts
(pitch 5.0&5.75)
12 12 contacts
(pitch 10.0)

0 5.0/.197"
1 10.0/.394"
8 5.75/.226"

0 L=12.5mm(Φ1.3)(DIMA=3.5)
1 L=13.0mm(UpΦ1.3 DownΦ1.0)(DIMA=4.3)
2 L=12.5mm(UpΦ1.3 DownΦ1.0)(DIMA=3.5)
3 L=11.5mm(Φ1.3)(DIMA=1.9)
4 L=14.2mm(Φ1.3)(DIMA=2.9)
5 L=17.5mm(Φ1.3)(DIMA=3.5)
6 L=20.0mm(Φ1.3)(DIMA=3.5)
7 L=18.0mm(UpΦ1.3 DownΦ1.0)(DIMA=3.5)
8 L=16.2mm(UpΦ1.3 DownΦ1.0)(DIMA=3.5)
9 L=16.5mm(Φ1.3)(DIMA=3.5)
A L=21.0mm(Φ1.1)(DIMA=4.4)
C L=12.7mm(Φ1.1)(DIMA=4.4)
D L=16.3mm(Φ1.1)(DIMA=4.4)
F L=12.5*8.8mm Bend pin(Φ1.3)
J L=13.0mm pin(Φ1.3)(DIMA=3.5)
H L=25.5mm pin(Φ1.3)(DIMA=3.5)
G L=17.9mm pin(Φ1.10)(DIMA=4.4)
K L=12.0mm pin(UpΦ1.3 DownΦ1.0)(Round pin)
M L=11.8mm pin(Φ1.1)(DIMA=4.0)
U L=25.1mm pin(Φ1.0)(DIMA=4.0)

0 Tin
1 Gold plating 10u"
2 Gold flash

0 PA66
1 PA46

0000 Standard

Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy