

OQ

XX

Number of contacts

X

Pitch

X

Body type

X

Color

X

PCB mounting

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
.. ...
24 24 contacts
16 16 contacts
(pitch 7.5&7.62)

B 2.5/.098"
1 3.5/.138"
3 3.81/.15"
7 5.0/.197"
5 5.08/.20"
A 7.5/.295"
0 7.62/.30"

0 Open
(pitch 5, 0/7.5/7.62)
1 Close
(pitch 2.5/5, 0/7.5/7.62)
2 Close
(pitch 3.5/3.81)
3 Open
(pitch 5, 08)
4 Close
(pitch 5, 08)
5 With flange
(pitch 3.5/3.81/5.0/5.08/7.5/7.62)

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0 Vertical
1 Right angle

0000 Standard

Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy