

KT

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Body type

X

X

X

X

X

Solid Block
02 2 contacts
03 3 contacts
.. ..
16 16 contacts

0 7.62/.30"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp
2 "*" Posidriv screw
W/Brass Machined Clamp

0 Black
5 Green (RAL 6018/T)
6 Blue
8 Grey (RAL 7035/D)
C Green (RAL 6018/U)

0 W/O flange
2 With flange nut
3 W/flange nut & W/handle
(only 3p & 4p)
4 With flange screw
5 W/flange screw & W/handle
(only 3p & 4p)

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy

H ROHS compliant
(lead<1000ppm)
In copper alloy