

TB

XX
Number of contacts

X
Pitch

X
Screw&Clamp

X
Color

X
Tail length

X

X

X

X

X

End Stackable
02 2 contacts
03 3 contacts
... ..
24 24 contacts
(pitch 5.0&5.08)
12 12 contacts
(pitch 10.0&10.16)

0 5.0/.197"
1 10.0/.394"
2 5.08/.20"
3 10.16/.40"

0 "+/-" Combination type
W/Brass Machined Clamp
1 "-" Slotted screw
W/Brass Machined Clamp

0 Black
5 Green
(RAL 6018/T)
6 Blue
8 Grey
(RAL 7035/D)
C Green
(RAL 6018/U)

0 4.4mm
1 3.8mm
2 3.5mm

0000 Standard
(Steel screw plating Cr³⁺)
Any special item by
customer request,
please contact sales
department.

G ROHS compliant
(lead<4%)
In copper alloy