

TG

XX Number of contacts							X Pitch	X Screw&Clamp	X Color	X Tail length	X Special insulator	X	X	X	X
0 5.0/.197"	1 10.0/.394"	5 5.08/.20"	6 10.16/.40"	0 "+/-" Combination type W/Brass Machined Clamp	1 "-" Slotted screw W/Brass Machined Clamp	0 Black 5 Green (RAL 6018/T) 6 Blue 8 Grey (RAL 7035/D) C Green (RAL 6018/U)	0 4.5mm 3 3.2mm	B Stackable (long-interlock) C Solid block (long-interlock) (only pitch 5.0)	000 Standard (Steel screw plating Cr ³⁺) Any special item by customer request, please contact sales department.	G ROHS compliant (lead<4%) In copper alloy	H ROHS compliant (lead<1000ppm) In copper alloy				